



■寸法表

呼び容量	A	B
50mL	26	86
100mL	56	116
150mL	86	146
300mL	186	246
500mL	276	336

■仕様

	50mL	100mL	150mL	300mL	500mL
材質	PMMA	PMMA	PMMA	PMMA	PMMA
呼び容量	50mL	100mL	150mL	300mL	500mL
外形寸法	48x26	64x56	86x86	146x186	246x276
質量	約10g	約20g	約30g	約60g	約100g

ガス置換対応 携帯真空サンプリングボックス

オールアクリル製で視認性・気密性に優れた超小型・軽量の持ち運びに便利な真空サンプリングボックス。バルブを標準装備し、減圧ガス置換が可能。

素材	
カタログページ番号	070
商品グループ番号	G-19926

商品	標準小売価格	入数																																																
<p>丸型50mL</p> <p>品番：19927</p> <p>主な仕様：呼称：丸型50mL/内寸法 (mm)：φ48×26H</p> <p>■寸法表</p> <table border="1"> <thead> <tr> <th>呼び容量</th> <th>A</th> <th>B</th> </tr> </thead> <tbody> <tr> <td>50mL</td> <td>26</td> <td>86</td> </tr> <tr> <td>100mL</td> <td>56</td> <td>116</td> </tr> <tr> <td>150mL</td> <td>86</td> <td>146</td> </tr> <tr> <td>300mL</td> <td>186</td> <td>246</td> </tr> <tr> <td>500mL</td> <td>276</td> <td>336</td> </tr> </tbody> </table> <p>■仕様</p> <table border="1"> <thead> <tr> <th></th> <th>50mL</th> <th>100mL</th> <th>150mL</th> <th>300mL</th> <th>500mL</th> </tr> </thead> <tbody> <tr> <td>材質</td> <td>PMMA</td> <td>PMMA</td> <td>PMMA</td> <td>PMMA</td> <td>PMMA</td> </tr> <tr> <td>呼び容量</td> <td>50mL</td> <td>100mL</td> <td>150mL</td> <td>300mL</td> <td>500mL</td> </tr> <tr> <td>外形寸法</td> <td>48x26</td> <td>64x56</td> <td>86x86</td> <td>146x186</td> <td>246x276</td> </tr> <tr> <td>質量</td> <td>約10g</td> <td>約20g</td> <td>約30g</td> <td>約60g</td> <td>約100g</td> </tr> </tbody> </table>	呼び容量	A	B	50mL	26	86	100mL	56	116	150mL	86	146	300mL	186	246	500mL	276	336		50mL	100mL	150mL	300mL	500mL	材質	PMMA	PMMA	PMMA	PMMA	PMMA	呼び容量	50mL	100mL	150mL	300mL	500mL	外形寸法	48x26	64x56	86x86	146x186	246x276	質量	約10g	約20g	約30g	約60g	約100g	24,600円	1台
呼び容量	A	B																																																
50mL	26	86																																																
100mL	56	116																																																
150mL	86	146																																																
300mL	186	246																																																
500mL	276	336																																																
	50mL	100mL	150mL	300mL	500mL																																													
材質	PMMA	PMMA	PMMA	PMMA	PMMA																																													
呼び容量	50mL	100mL	150mL	300mL	500mL																																													
外形寸法	48x26	64x56	86x86	146x186	246x276																																													
質量	約10g	約20g	約30g	約60g	約100g																																													